

DESCRIPTION

- Metal construction with a chrome finish
- R1/2 inlet connections
- Thermostatic valve design and with 5 fuctions handheld shower
- 1750mm shower hose

OPERATION

- Round style handle with a knob
- Temperature lever operates through a 230 degree arc with maximum cold at full clockwise rotation and maximum hot at full counterclockwise rotation
- Pull out Safety stop design preset temperature at 38° C
- Safety stop override allows maximum temperature at 49° C
- Factory established temperature range from 20° C to 49° C

CARTRIDGE


- 143910 thermostatic cartridge design with Nonmetallic / non- ferrous material

STANDARD

- Designed to meet GB18145-2003 and QB2806-2006 standard





WARRANTY

- 5 years limited warranty against leaks and drips



Thermostatic
Two-Handle Wall Mount Tub Shower

Models: 58332



Usage of controlling water flow

1. Turn the left handle anticlockwise to open water flow; Turn the left handle clockwise to close water flow;
2. Turn the handle up, water temperature will turn to 20° C from 38° C;
3. Pull out right side handle first and turn it down, water temperature will turn to 49° C from 38° C.

CRITICAL DIMENSION

(DO NOT SCALE)

5 Function Handheld Shower

- Dripping
- Shower spray
- Showerspray & revolving massage
- Revolving massage
- Aeration



Dripping




Shower spray






Showerspray &
revolving massage



Revolving
massage



Aeration



CRITICAL DIMENSION
(DO NOT SCALE)

